

## SIEVES. 20/30cm DIA BRASS FINE SERIES.

As Per IS 460 (Part I) - 1962.

Made of Brass Frame, without joint.

Following apertures are available in 20cm & 30cm Dia Sieves.



| ORDER CODE                         | BSS MESH No. | ASTM MESH No. | ISS MESH No. | WIDTH OF APERTURE |
|------------------------------------|--------------|---------------|--------------|-------------------|
| AIC-SFS-20B4.75 / AIC-SFS-30B4.75. | -            | 4             | -            | 4.75mm            |
| AIC-SFS-20B4.00 / AIC-SFS-30B4.00. | 4            | 5             | 480          | 4.00mm            |
| AIC-SFS-20B3.35 / AIC-SFS-30B3.35. | 5            | 6             | 340          | 3.35mm            |
| AIC-SFS-20B2.80 / AIC-SFS-30B2.80. | 6            | 7             | 280          | 2.80mm            |
| AIC-SFS-20B2.36 / AIC-SFS-30B2.36. | 7            | 8             | 240          | 2.36mm            |
| AIC-SFS-20B2.00 / AIC-SFS-30B2.00. | 8            | 10            | 200          | 2.00mm            |
| AIC-SFS-20B1.70 / AIC-SFS-30B1.70. | 10           | 12            | 170          | 1.70mm            |
| AIC-SFS-20B1.40 / AIC-SFS-30B1.40. | 12           | 14            | 140          | 1.40mm            |
| AIC-SFS-20B1.18 / AIC-SFS-30B1.18. | 14           | 16            | 120          | 1.18mm            |
| AIC-SFS-20B1.00 / AIC-SFS-30B1.00. | 16           | 18            | 100          | 1.00mm            |
| AIC-SFS-20B850M / AIC-SFS-30B850M. | 18           | 20            | 85           | 850microns        |
| AIC-SFS-20B710M / AIC-SFS-30B710M. | 22           | 25            | 70           | 710microns        |
| AIC-SFS-20B600M / AIC-SFS-30B600M. | 25           | 30            | 60           | 600microns        |
| AIC-SFS-20B500M / AIC-SFS-30B500M. | 30           | 35            | 50           | 500microns        |
| AIC-SFS-20B425M / AIC-SFS-30B425M. | 36           | 36            | 40           | 425microns        |
| AIC-SFS-20B355M / AIC-SFS-30B355M. | 44           | 45            | 35           | 355microns        |
| AIC-SFS-20B300M / AIC-SFS-30B300M. | 52           | 50            | 30           | 300microns        |
| AIC-SFS-20B250M / AIC-SFS-30B250M. | 60           | 60            | 25           | 250microns        |
| AIC-SFS-20B212M / AIC-SFS-30B212M. | 72           | 70            | 20           | 212microns        |
| AIC-SFS-20B180M / AIC-SFS-30B180M. | 85           | 80            | 18           | 180microns        |
| AIC-SFS-20B150M / AIC-SFS-30B150M. | 100          | 100           | 15           | 150microns        |
| AIC-SFS-20B125M / AIC-SFS-30B125M. | 120          | 120           | 12           | 125microns        |
| AIC-SFS-20B106M / AIC-SFS-30B106M. | 150          | 140           | 10           | 106microns        |
| AIC-SFS-20B090M / AIC-SFS-30B090M. | 170          | 170           | 9            | 90microns         |
| AIC-SFS-20B075M / AIC-SFS-30B075M. | 200          | 200           | 8            | 75microns         |
| AIC-SFS-20B063M / AIC-SFS-30B063M. | 240          | 230           | 7            | 63microns         |
| AIC-SFS-20B053M / AIC-SFS-30B053M. | 300          | 270           | 6            | 53microns         |
| AIC-SFS-20B050M / AIC-SFS-30B050M. | -            | -             | -            | 50microns         |
| AIC-SFS-20B045M / AIC-SFS-30B045M. | 350          | 325           | 4            | 45microns         |
| AIC-SFS-20B040M / AIC-SFS-30B040M. | -            | -             | -            | 40microns         |
| AIC-SFS-20B038M / AIC-SFS-30B038M. | 400          | 400           | -            | 38microns         |
| AIC-SFS-20B032M / AIC-SFS-30B032M. | 450          | -             | -            | 32microns         |
| AIC-SFS-20B025M / AIC-SFS-30B025M. | 500          | -             | 2            | 25microns         |
| AIC-SFS-20B020M / AIC-SFS-30B020M. | 635          | -             | -            | 20microns         |
| AIC-SFS-20BLP / AIC-SFS-30BLP.     | Lid – Pan.   |               |              |                   |